

# CA® POWER GRIP

## CA® POWER GRIP set

CA® POWER GRIP silicone forms enable the fabrication of individual attachments for the CA® CLEAR ALIGNER technology. The set contains nine different moulds that can be filled with light-curing composite for direct application on the prepared tooth as well as two appropriate stainless steel holders for positioning CA® POWER GRIP moulds.



## CA® POWER GRIP MFM

MFM (multifunctional forced movement): is used for extrusion and mesial/distal rotation. For use with CA® splints and elastics.



## CA® POWER GRIP MDI

MDI (mesial/distal inclination): enables setting upright frontal teeth and for mesial/distal inclination.



## CA® POWER GRIP DMI

DMI (distal mesial inclination): enables setting upright frontal teeth and for distal/mesial tooth inclinations.



## CA® POWER GRIP FALA

FALA (force application LABIAL): used for protrusion, retrusion and torque control up to 3°. For creation of activation surfaces on the teeth in the gingival area with labial placement – for teeth: 11, 13, 21, 23, 33 and 43.



## CA® POWER GRIP FALI

FALI (force application LINGUAL): used for protrusion, retrusion and torque control up to 3°. For creation of activation surfaces on the teeth in the gingival area with labial, lingual and palatal placement – for teeth: 12, 22, 31, 32, 41 and 42.

Learn more:



CA® CLEAR ALIGNER



### CA® POWER GRIP BUB

BUB (Build-Up bicuspid): round pad for molars (3 mm) used for occlusal bite elevation (approx. 2 mm).



### CA® POWER GRIP BUAS

BUAS (Build-Up anterior small, width 2 mm): used as intrusion plateau for the treatment of deep bite. Helps maintaining intrusion forces while the patient is not wearing the CA® CLEAR ALIGNER, allows molar extrusion.



### CA® POWER GRIP BUAL

BUAL (Build-Up anterior large, width 4 mm) also serves as intrusion plateau for the treatment of deep bite, width adjusted to front teeth with larger palatal surface.



### CA® POWER GRIP BUM

BUM (Build-Up molar): oval molar pad (3 × 5 mm) used for occlusal bite elevation (approx 2 mm).



### CA® POWER GRIP holder

For positioning CA® POWER GRIP silicone moulds. Stainless steel, sterilisable.

<p>/// CA® POWER GRIP set incl. 2 holders and 18 silicone moulds (9 versions, 2 pieces each), instructions and CD</p>	<p><b>5338.1</b> 1 kit</p>
<p>/// CA® POWER GRIP MFM</p>	<p><b>5330.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP MDI</p>	<p><b>5331.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP DMI</p>	<p><b>5332.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP FALA</p>	<p><b>5333.1</b> 2 pieces</p>

<p>/// CA® POWER GRIP FALI</p>	<p><b>5334.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP BUB</p>	<p><b>5335.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP BUM</p>	<p><b>5336.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP BUAS</p>	<p><b>5337.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP BUAL</p>	<p><b>5339.1</b> 2 pieces</p>
<p>/// CA® POWER GRIP holder one holder each for frontal and posterior region, stainless steel, sterilisable</p>	<p><b>5340.1</b> 2 pieces</p>